

## **HELIO-STROB** master

... caters for all needs



- high and constant brightness
- pin sharp images
- easy to operate via touch panel
- internal and external triggering, mains synchronous triggering
- TTL-output
- slow-motion function
- electronic positioning (phase shifting)
- dimmer function
- serial interface (USB)



## **HELIO-STROB** master

## **Applications**

By means of extremely short flash impulses the HELIO-STROB master allows the observation of very rapid processes with the naked eye. It provides pin sharp images of the apparently stationary object: the "stroboscopic effect". All functional adjustments can comfortably be set via the touch panel and the twist knob. When analysing fast processes such as rotation or vibration the standard features "slow motion" and "position" (phase shifting) put even the smallest detail into perspective. The finely graduated dimmer function allows an adjustment of the light intensity and thus enables fatigue-free observation to the smallest detail. The flash frequency can either be controlled by the accurate internal trigger, by an external trigger or even by mains synchronous triggering. Thanks to the integrated prescaler external impulses are processed up to a frequency of 8000 Hz\*. Proximity switches and optical sensors can directly be con-







External triggering up to 8000 Hz

nected to the stroboscope. Other promising new features allow the adaptation to individual gear ratios – even those of variable transformation ratios. The serial interface allows a direct communication to the PC – thus all parameters can be remotely controlled and exported. Using the "hotkey" function the new software "SpeedDoC" transmits the current measuring value to the corresponding cursor position in your test report.



## **Technical Data**

Power supply Power consumption Housing

Weight

Light source Frequency range in Hz/min<sup>-1</sup> Internal control of the flash rate External control of the flash rate

Measured value display

Resolution of the display Phase shifting Slow motion function

Serial interface Light output Light intensity Operating temperature Storage temperature Air humidity Certification Art.-No.

115/230 VAC, 50 - 60 Hz approx. 150 VA metal case with handle / support 280 x 240 x 80 (mm) hand lamp:  $182.5 \times 117 \times 117 \text{ (mm)}$ approx. 2.8 kg (control unit) approx. 1.5 kg (hand lamp) flash tube, plug-in installation 1 - 315 Hz/60 - 18900 min-1 twist knob and touch panel external transducer, pos. impulses, 50 mV - 30 V, input frequency 8000 Hz\* max., variable transformation ratio 1:10 - 10:1 LC display, 64 x 36 mm display in Hz/fpm 0.01 Hz/up to 0.1 fpm  $0^{\circ} - 540^{\circ}/0 - 999.99 \text{ ms}$ beat frequency -5.00 Hz up to +5.00 HzUSB (type B) 3.0 Ws max. 9600 Lux max. (at a distance of 50 cm) 0° ... +40° C max. 80 % relative air humidity at 30° C

-20° ... +85° C

CF

0300330020



Revisions in the course of technical progress reserved. \*with integrated frequency scaler

